



A Woman's Touch

Name	Flat Width (cm)	Flat Length (cm)	Thin Score*,**	Contoured	Extra Feature	Color
LATEX						
Ansell Midnight	5.3	20.6	2, thin, average	no	roomy head	black
Beyond 7	5.3	20.5	1, very thin	no		blue
Beyond 7 Aloe Lube	5.4	20.2	1	no	aloe lube	green
Beyond 7 Studded	5.0	19.0	1	no	studded (out)	vanilla
Crown	5.2	21.6	1	no		pink
Crown Colors	5.2	21.2	1	no		asst colors
Diva Contoured & Textured	5.3	21.4	4, very thick	slightly	ribs/studs (out) sturdy pkg	vanilla
Diva Studded	5.4	21.4	3, thick	no	studs (out) sturdy pkg	vanilla
Diva XL Studded	5.5	21.0	3	no	ribs/studs (out) sturdy pkg	vanilla
Diva Xtra Sensitive	5.4	21.6	2	no	sturdy pkg	vanilla
Durex Love	5.8	22.0	1	no		vanilla
Durex Unlubed	5.4	22.5	2	no	unlubed	vanilla
Glyde Vegan	5.3	21.0	1	no	vegan	clear
Kimono Maxx	5.3	21.5	1	no		vanilla
Kimono Microthin	5.0	20.5	1	yes		vanilla
Kimono Micro Aqua Lube	5.0	21.3	1	yes	aqua lube	vanilla
Kimono Microthin Large	5.4	21.7	1	no		clear
Kimono Type E	5.2	21.4	1	yes	studs (out)	green
LifeStyles Kiss Of Mint	6.3	20.5	2	no	mint powder roomy head	vanilla
Night Light	5.4	20.3	4	no		glows green
Pleasure Plus	5.2	21.0	2	yes	head pouch	vanilla
Trojan Inspiral	5.1	19.3	4	yes	head pouch	clear
Trojan Magnum	6.0	21.5	3	no	1 rib	vanilla
Trojan Magnum XL	6.2	21.7	3	no		vanilla
Trustex Flavored	5.4	21.5	3	no	asst flavors	asst colors
Trustex Unlubed	5.3	18.5	3	no	unlubed	asst colors
NON-LATEX						
Avanti Polyurethane	6.2	20.4	3	no	inflexible polyurethane	clear
Trojan Supra Polyurethane	5.7	21.2	1	no	inflexible polyurethane	clear
Skyn Polyisoprene	5.3	20.5	1	no	flexible polyisoprene	clear
Female Condom	8.0	18.4	3, but 0 for male	no	wm controlled polyurethane	clear

***THIN SCORE:** 1) AWT carries the strongest, thinnest condoms on the market, so even our thickest condoms are often thinner than most widely available condoms. Therefore, don't necessarily avoid a '4', as it may have other redeeming features that will meet your pleasure needs.

****THIN SCORE:** 2) Thicker condoms may seem more durable, but studies show that they are not when looking only at thickness. What makes a stronger condom is the manner in which they are manufactured and tested, so very thin--and well made--condoms are safer for your use, and more pleasurable for use. Choose a condom based on the overall features, not simply the thickness/thinness score. (And never wear two condoms "for safety's sake"--two are NOT safer than one good, lubed condom. Two condoms rub against each other and dramatically increase the break rate.)

FLAT WIDTH AND LENGTH: All condoms were measured at collapsed flat states to standardize the comparison. The best way to use these numbers is to wear/use a condom once, decide whether you liked it, and vary your choices from there. This is because the FLAT WIDTH and LENGTH is only for comparison, not an actual size. For example, the Beyond 7 has a flat width of 5.3 cm (2.1 in). When worn, the unstretched diameter is 12.8cm (5.1 in). When the flat length of the Beyond 7 (20.5cm/8 in) is compared to a worn version, the unstretched length (worn) shortens to 16.5cm/6.5 in.

STRETCHING CONDOMS: For most people, condoms are more comfortable to wear when they are not stretched tightly. This is because a gently mobile condom gently carries the wearer, and adds stimulation rather than dampening it. Too much movement can cause the condom to slip off, or be uncomfortable for the person being penetrated (too much friction). Finding the right size, thickness and snugness (and perhaps color!) can make a vast difference in functional comfort. All condoms are more comfortable and durable when lubricant is added to the inside tip, and to the outside shaft. As a general rule, latex condoms will stretch more than polyurethane, but often condoms are more comfortable when worn just slightly stretched, rather than taughtly stretched. This means that choosing a condom that "fits snugly and comfortably" will function better in safety and pleasure than one worn too snugly.

CONTOURED: Some enjoy the sensation of a condom which hugs the penis, either because it increases the sensation for the male wearing it, or because it reduces the friction for the person being penetrated. The "head pouch" shape allows more latex movement (and sensation) around the head of the penis, which may vastly increase the pleasure of the wearer. Too much "head pouch" latex may increase friction uncomfortably for the person being penetrated, so testing is definitely advised.